

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Socket RJ45 category 6 FTP 1 module mat black

REF. 079162L | EAN KODA. 3414971637771

> [The product details page](#)

Značilnosti izdelka:

- Category 6 FTP : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds. Shielded socket.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Gold/nickel contacts, thickness of gold minimum 0,8em
- 1 module
- Mat Black

Priporočila / omejitve

- Clean the surface with a cloth. Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Prednosti montaže:

- RJ45 connectors are equipped with a locking nut. They do not require a special tool and can be re-wired if a mistake is made.

Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Dokumentacija

Tehnična dokumentacija

-  F00949FR-08.pdf | PDF (0.78Mo)
-  LE01557AK.pdf | PDF (1.59Mo)
-  LE01557AJ.pdf | PDF (1.55Mo)
-  F00949EN-08.pdf | PDF (0.78Mo)

CAD & specifikacije načrtov / BIM

-  3D_LG-079162L.stp | IFC (18.06Mo)
- BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)
- BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

Katalog & drugo

-  ex223001_1188.pdf | PDF (0.12Mo)
-  ex223001_0986.pdf | PDF (0.11Mo)

Pogodbe in certifikati

-  LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)
-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-PL3_Cat6_FTP_32756_ac1181022 | (0.07Mo)
-  LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)
-  AoC-PL2_Cat6FTP3275632856ac1181020 | (0.07Mo)
-  AoC-SA52_SB52_ac109588 | (0.06Mo)



AoC-CL2_Cat6FTP3275632856ac1181021 | (0.07Mo)