

Naziv PDF datoteke



EMDX³ LEGRAND

eDMX³ energy meter tri direct 63A 230/400V 2tariff
RS485 MID

REF. 412093 | EAN KODA. 3414971413931

> [The product details page](#)

Značilnosti izdelka:

- Direct connection up to 63A 3P or 3P+N.
- Communication : Modbus RS 485.
- Double tariff or Pulse input to collect other meter (gas, water, electrical meters).
- MID Certified.
- Bidirectional measure of production and consumption energies.

Prednosti montaže:

- Simple installation by direct connection up to 63A without the use of a current transformer. Easy connection of communication thanks to removable connectors. One input connector for double tariff or Pulse input to collect water or gas meters without using added concentrator device.

Prednosti uporabe:

- Backlit display and simple access to easy reading of data. Pre-visualization of parameters. Settings mode protected by user code Bidirectional measure of production and consumption energies

Edinstvene značilnosti:

- Measure of run hours on each tariff.
- Phaseshift measure locally displayed.

Dokumentacija

Tehnična dokumentacija

- IDP000196_F02840EN_04.pdf | PDF (4.16Mo)
- F02840EN_01.pdf | PDF (3.79Mo)
- IDP000196_F02840_04.pdf | PDF (1.83Mo)
- EXB20057_FR.pdf | PDF (10.47Mo)
- PR_412093.pdf | PDF (0.28Mo)
- EXB20058_EN.pdf | PDF (10.42Mo)
- IDP000370.pdf | PDF (0.28Mo)
- EXB20065_GT_EMDX3_compteurs-energie_FR.pdf | PDF

Katalog & drugo

- ex223001_0120.pdf | PDF (0.06Mo)
- ex223001_0118.pdf | PDF (0.12Mo)

(3.04Mo)

 EXB20066_TG_EMDX3_Electricity_meters_EN.pdf | PDF
(3.04Mo)

 LE11297BA.pdf | PDF (1.69Mo)

 LE11299BD.pdf | PDF (1.77Mo)

 LE11297BB.pdf | PDF (1.44Mo)

CAD & specifikacije načrtov / BIM

 412090.dwg | DWG (0.11Mo)

Pogodbe in certifikati

 PEP_LGRP-01747-V01.01-EN_EMDX3.pdf | PDF (0.82Mo)