

Naziv PDF datoteke



LINKEO LEGRAND

Linkeo 19 inches freestanding cabinet with single front glass door capacity 42U 600x1000mm ready-assembled

REF. 646762 | EAN KODA. 3414971001565

> [The product details page](#)

Značilnosti izdelka:

- Capacity 42U, dimensions (HxWxD) : 2026 x 600 x 1000mm
- 4 sides locked with key lock to ensure security
- Metal structure provides IP20 (protected against solid objects larger than 12.5 mm in diameter) and IK08 (protected against mechanical impact with an energy of 5 joules) protection.
- Reversible single front glass door with screen printing, equipped with a locking bolt and 2 metal hinges
- Panels with automatic equipotential connection

Priporočila / omejitve

- This freestanding cabinet is intended for digital infrastructures. It has a permissible load up to 400 kg. Linkeo 19" freestanding cabinets can be integrated in installations complying with the following standards : EN 50173-1, EN 50174-1 & 2, C 90-480-1 & 2, ISO IEC 11801, NF C 15-100, IEC 60364-4-41

Prednosti montaže:

- The whole structure stands on 4 levelling feet that can be adjusted from the inside and the outside of the cabinet. Ready-assembled.

Prednosti uporabe:

- Equipped with 2 x 19 inches uprights with U marking and adjustable in depth

Edinstvene značilnosti:

- Continuity of the cabinet metal conductive parts is achieved by design. Removable side and rear panels have automatic grounding to avoid any risk after maintenance
- Protected against solid objects larger than 12.5 mm (IP20) and mechanical impact with an energy of 5 joules (IK08)
- The textured polyester coating provides an excellent resistance to corrosion and scratching

Dokumentacija

Tehnična dokumentacija

 F02420EN-01.pdf | PDF (2.28Mo)

 F02420FR-01.pdf | PDF (2.28Mo)

 LE09825AA-03.pdf | PDF (1.09Mo)

CAD & specifikacije načrtov / BIM

Legrand_Baies_Linkeo_avec_porte_avant_simple_largeur_600.rfa
| RFA (5.12Mo)

Legrand_Linkeo_Freestanding_cabinets_with_single_front_door_widt

Katalog & drugo

 ex223001_0943.pdf | PDF (0.07Mo)

 ex223001_0944.pdf | PDF (0.14Mo)

Pogodbe in certifikati

 LGRP-00841-V01.01-EN.pdf | PDF (0.61Mo)

h_600.rfa | RFA (5.12Mo)