

Naziv PDF datoteke



BELANKO S LEGRAND

Belanko S - 2 gang double pole switch - 45A + BS switched socket outlet neon with cooker marking - 13A - Anthracite

REF. 617778 | EAN KODA. 3414971688131

> [The product details page](#)

Značilnosti izdelka:

- British Standard, 13A, 250V + 45A Switch
- Sold with white BELANKO S plate
- Screw type terminals for enhanced contacts
- Marked terminals for easy identification
- Red Rocker with red light indicator

Priporočila / omejitve

- Recommended inside use only

Prednosti montaže:

- Quick & Easy plate clipping system

Prednosti uporabe:

- Complies to British Standards certifications for heavy loads. Fitted with safety shutters to maximise child protection

Edinstvene značilnosti:

- Fast and Easy install. Paint job made simpler thanks to protective shell
- Optimised range for new builds and ideal for renovation projects
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Dokumentacija

Tehnična dokumentacija

F02972EN-01.pdf | PDF (1.39Mo)

Pogodbe in certifikati

OC / CB-FR_706749 | (0.31Mo)

OC / CB-FR_706749M1 | (0.56Mo)

G-MARK-0032-1873-V-1 | (11.21Mo)

OC / CB-FR_719319 | (0.72Mo)

OC / CB-FR_719316 | (0.77Mo)

AoC-2401B1479SHA-V1 | (0.77Mo)

Katalog & drugo

ex223001_0670.pdf | PDF (0.06Mo)