

Naziv PDF datoteke



PLEXO™ LEGRAND

Plexo™ - 3-gang surface box with 5 membrane glands (4x1 entry + 1x2 entries) - Horizontal and vertical - IP55 - Anthracite

REF. 069603L | EAN KODA. 3414971879904

The anthracite waterproof 3-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). This box conception gives the opportunity to install it horizontally or vertically. For indoor or outdoor use.

> [The product details page](#)

Splošni opis:

The anthracite waterproof 3-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). This box conception gives the opportunity to install it horizontally or vertically. For indoor or outdoor use.

Značilnosti izdelka:

- Surface box to install functions supplied in composable mode (mechanism products).
- IP55 : protected against dust and water spary from all directions.
- Plastic materials with reinforced UV protection

Prednosti montaže:

- A two-part box : a thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring (the flexible part on the back of the product adapts to the shape of the wall) and a frame, to be clipped on the mounting plate.

Prednosti uporabe:

- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

Edinstvene značilnosti:

- The box is composed of a mounting plate and a frame. The thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring. The flexible part on the back of the product adapts to the shape of the wall.
- The box can be used for both vertical and horizontal installation thanks to the 90° symmetrical mechanisms.

Dokumentacija

Tehnična dokumentacija

 F03421EN-02.pdf | PDF (1.91Mo)

 F03421FR-02.pdf | PDF (1.9Mo)

Pogodbe in certifikati

 MEEI-UP 69267307 002 | (1.25Mo)

 LGRP-01292-V02.01-FR.pdf | PDF (0.82Mo)

CAD & specifikacije načrtov / BIM

 3D_LG-069603L.stp | IFC (1.32Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

	NF App Domestic-NF012_3249/A1 (0.7Mo)
	AENOR-030/002621 (0.71Mo)
	VDE-40057978 (1.18Mo)
	NF App Domestic-NF012_3294/A2 (0.74Mo)
	OC / CB-FR_715939 (0.64Mo)
	OC / CB-FR_718712/A1 (0.55Mo)
	MEEI-UP 69267307 001 (1.57Mo)
	MEEI-UP 69267307 003 (1.57Mo)
	OC / CB-FR_715726 (0.74Mo)