

Naziv PDF datoteke



PLEXO™ LEGRAND

Plexo™ - 1-gang surface box with 2 membrane glands (2 x 1 entry) - IP55 - Grey

REF. 069651L | EAN KODA. 3414971880863

The grey waterproof 1-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). The box conception gives the opportunity to wire the mechanism from the top, bottom, sides or back. For indoor or outdoor use.

> [The product details page](#)

Splošni opis:

The grey waterproof 1-gang box Plexo allows a surface mounting of all Plexo functions (mechanism products). The box conception gives the opportunity to wire the mechanism from the top, bottom, sides or back. For indoor or outdoor use.

Značilnosti izdelka:

- Surface box to install functions supplied in composable mode (mechanism products).
- IP55 : protected against dust and water spary from all directions.
- Plastic materials with reinforced UV protection

Prednosti montaže:

- A two-part box : a thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring (the flexible part on the back of the product adapts to the shape of the wall) and a frame, to be clipped on the mounting plate.

Edinstvene značilnosti:

- The box is composed of a mounting plate and a frame. The thin and very rigid mounting plate allows an easy fixing and a freedom of movement for wiring. The flexible part on the back of the product adapts to the shape of the wall.
- The mechanism is fixed to the mounting plate symmetrically at 90°, allowing cables/tubes to be fed in from the top, bottom, right or left, while maintaining the standard vertical position of the button.

Dokumentacija

Tehnična dokumentacija

 F03421EN-02.pdf | PDF (1.91Mo)

 F03421FR-02.pdf | PDF (1.9Mo)

CAD & specifikacije načrtov / BIM

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

 3D_LG-069651L.stp | IFC (0.77Mo)

Katalog & drugo

 ex223001_0795.pdf | PDF (0.15Mo)

Pogodbe in certifikati

 MEEI-UP 69267307 002 | (1.25Mo)

 LGRP-01312-V02.01-FR.pdf | PDF (0.77Mo)

 AENOR-030/002621 | (0.71Mo)

 OC / CB-FR_715939 | (0.64Mo)

	MEEI-UP 69267307 001 (1.57Mo)
	LGRP-01513-V02.01-FR.pdf PDF (0.75Mo)
	Decl. UE RED-A 4044 C (0.45Mo)
	OC / CB-FR_715726 (0.74Mo)
	LGRP-01292-V02.01-FR.pdf PDF (0.82Mo)
	NF App Domestic-NF012_3249/A1 (0.7Mo)
	VDE-40057978 (1.18Mo)
	NF App Domestic-NF012_3294/A2 (0.74Mo)
	OC / CB-FR_717742 (0.53Mo)
	OC / CB-FR_718712/A1 (0.55Mo)
	Decl. UE RED-A 4228 A (0.45Mo)
	NF App Domestic-NF012_4184 (0.5Mo)
	MEEI-UP 69267307 003 (1.57Mo)
	OC / CB-DE 2-039435-M1 (0.63Mo)
	OC / CB-FR_718017 (0.32Mo)
	OC / CB-FR_719272 (0.33Mo)