

Naziv PDF datoteke



LEGRAND

Plexo™ - RJ 45 socket category 6A STP IP55 with closed shutter IK07 Grey mechanism

REF. 069559L | EAN KODA. 3414971878921

> [The product details page](#)

Značilnosti izdelka:

- Category 6A STP : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second. Shielded socket. Body and spreader made of metal alloy with copper/nickel coating.
- High protection against water and dust. Suitable for garages, cellars , parkings, industrial areas, and outdoor environment (terrace, gardens, campings...)
- Grey mechanism

Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C

Prednosti montaže:

- Can be integrated in all supports. Contacts marked with dual colour code and wiring schemes T568 A and T 568 B.

Prednosti uporabe:

- Connector with fast connection thanks to integrated crimping take AWG 22 single-core cables up to AWG 26 and AWG multicore cables

Edinstvene značilnosti:

- Fast-connection tool-free sockets with connector
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.

Dokumentacija

Tehnična dokumentacija

 F03585EN-00.pdf | PDF (1.89Mo)

 LE11720AA_2.pdf | PDF (2.24Mo)

 F03585FR-00.pdf | PDF (1.88Mo)

CAD & specifikacije načrtov / BIM

 3D_LG-069559L.stp | IFC (1.36Mo)

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

Katalog & drugo

 ex223001_0794.pdf | PDF (0.11Mo)

 ex223001_0982.pdf | PDF (0.08Mo)

Pogodbe in certifikati

 LGRP-01403-V01.01-EN.PDF | PDF (0.63Mo)

 LGRP-01403-V01.01-FR.pdf | PDF (0.65Mo)