

Naziv PDF datoteke



LEGRAND

Fuse carrier 1P+N for industrial cylindrical cartridge fuse 10 x 38 mm

REF. 005818 | EAN KODA. 3245060058180

> [The product details page](#)

Značilnosti izdelka:

- With insulated carrier class II, padlockable with Accessory 005799
- Terminals capacity 1 x 16 mm² maxi, IP 2X, screw head PZ1
- Conforms to IEC standards 60269 - 1, 60269 - 2, 60269 - 2 - 1 and standard NF C 63 - 210
- Possibility to signal indicator blown fuse with accessory 005790
- Fuse not supplied

Priporočila / omejitve

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Prednosti montaže:

- Fitted with two DIN rail clamps, one top side and one bottom side, allowing an independent removal of this product when the prong busbar supplying the row is still in place.

Prednosti uporabe:

- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit.

Dokumentacija

Tehnična dokumentacija

 FA222CEN_03.pdf | PDF (0.8Mo)

 FA222C_03.pdf | PDF (0.76Mo)

CAD & specifikacije načrtov / BIM

 005818.dwg | DWG (0.06Mo)

Katalog & drugo

 ex223001_0092.pdf | PDF (0.23Mo)

Pogodbe in certifikati

 LGRP-2015-149-V1-EN.pdf | PDF (0.62Mo)

