

Naziv PDF datoteke



LEGRAND

Stabilised mono switching power supply - 75-960 W - output 12 V= - 75 W

REF. 146613 | EAN KODA. 3414970543257

> [The product details page](#)

Značilnosti izdelka:

- Stabilised switched mode power supplies - single-phase - Conforming to standards UL 508, IEC EN 60950 - 1 and IEC EN 61204 - 3 - UL - approved in USA and Canada - Operating frequency : 50/60 Hz - Output voltage present indicator - Potentiometer for adjusting the output voltage on front panel - With signal or relay contact for feedback on the status of the active output voltage (except 75 W) - Connection with copper conductors only - For mounting on a symmetrical rail depth 7.5 mm and 15 mm
- Single-phase 75 - 960 W for loads with strong inrush current - Ability to supply temporary overcurrents (up to 150% for 3 sec) - High efficiency (up to 94%) - Low harmonic pollution due to the integrated PFC filter (from 120 W) - Adjustable output voltage - Aluminium casing Input voltage : 100 to 240 V~ Output voltage : 12 V - Nominal power : 75 W - Nominal rating : 6.3 A - Setting range : 12 to 14 V - Width : 32 mm

Dokumentacija

Tehnična dokumentacija

-  F02124FR-00.pdf | PDF (0.93Mo)
-  F02124EN-00.pdf | PDF (0.86Mo)
-  LE07894AA-01.pdf | PDF (0.53Mo)

CAD & specifikacije načrtov / BIM

-  146622.dwg | DWG (0.07Mo)

Katalog & drugo

-  ex223001_0510.pdf | PDF (0.03Mo)
-  ex223001_0509.pdf | PDF (0.03Mo)
-  ex223001_0505.pdf | PDF (0.25Mo)
-  ex223001_0507.pdf | PDF (0.06Mo)

Pogodbe in certifikati

-  UL listed cULus-E223674 | (0.04Mo)