

Naziv PDF datoteke



LEGRAND

Stabilised mono/bi switching power supply - 120-480 W - output 24 V= - 480 W

REF. 146665 | EAN KODA. 3414970543554

> [The product details page](#)

Značilnosti izdelka:

- Stabilised switched mode power supplies - single/two - phase and three - phase - Conforming to standards UL 508, IEC EN 60950 - 1 and IEC EN 61204 - 3 - UL - approved in USA (and Canada for Cat. Nos. 1 466 54/63/82) - Operating frequency : 50/60 Hz - Output voltage present indicator - Potentiometer for adjusting the output voltage on front panel - Integrated short - circuit and overload protection - With signal or relay contact for feedback on the status of the active output voltage - Connection with copper conductors only - For mounting on a symmetrical rail depth 7.5 mm and 15 mm
- Single/two - phase 120 - 480 W wide input voltage range - Suitable for single or two - phase networks - Also suitable for three - phase networks, when using 2 phases only - Low harmonic pollution due to the integrated PFC filter (from 240 W) - Adjustable output voltage - Aluminium casingInput voltage : 200 to 500 V~ Output voltage : 24 V - Nominal power : 480 W - Nominal rating : 20 A - Setting range : 24 to 28 V - Width : 86 mm

Dokumentacija

Tehnična dokumentacija

-  F02125FR-00.pdf | PDF (0.72Mo)
-  LE07894AA-01.pdf | PDF (0.53Mo)
-  F02125EN-00.pdf | PDF (0.7Mo)

CAD & specifikacije načrtov / BIM

-  146625.dwg | DWG (0.08Mo)

Katalog & drugo

-  ex223001_0510.pdf | PDF (0.03Mo)
-  ex223001_0509.pdf | PDF (0.03Mo)
-  ex223001_0506.pdf | PDF (0.08Mo)
-  ex223001_0507.pdf | PDF (0.06Mo)

Pogodbe in certifikati

-  UL listed cULus-E223674 | (0.04Mo)