

# Naziv PDF datoteke



## LIVING NOW BTICINO

Living Now - lighted 4 ways switch, white light - 127V, 10AX, 1 module

REF. BT-K4004V127L | EAN KODA. 8005543647721

> [The product details page](#)

### Značilnosti izdelka:

- The mechanism is Full - touch enhancing the ergonomics of the command : it can be operated by pressing the control at any point on its surface (above, below and in the middle)
- Full touch also means perfect flatness of the control point regardless of the load status
- Screw and plate terminals
- Easy installation and removal of the mechanism on the support frame thanks to the new generation of plastic hooking system
- 10 AX, 127 Va.c. 1P Completed with a white LED for light signaling 127V

### Priporočila / omejitve

- For internal use only.

### Prednosti montaže:

- Further improvement of the installation and removal in the support frame thanks to the new generation of plastic hooks. The reduced depth of this device simplifies wall installation in case of shallow or full of cables boxes.

### Prednosti uporabe:

- Ergonomics is enhanced thanks to the new Full touch concept: the control can be operated by pressing at any point on its surface

### Edinstvene značilnosti:

- The interaction is immediate and thanks to the "full touch" controls, the ergonomics of the button are completely new. In fact it can't be operated in a precise way in any part thereof, at the center, top, or bottom. Once pressed, the key returns to position, remaining always perfectly aligned.
- The strength of design lies in the essentiality of the form obtained from the search for an absolute flatness between the elements of the switch.
- You can replace the device cover at any time by changing its color or restoring any damage to the surface without changing the entire device

## Dokumentacija

### Tehnična dokumentacija



IDP000270\_03-EN.pdf | PDF (0.11Mo)



LE10252AC.pdf | PDF (0.68Mo)

### Katalog & drugo



ex223001\_0766.pdf | PDF (0.08Mo)

CAD & specifikacije načrtov / BIM

BIM-BTICINO-LIVING-NOW-2025-ENGLISH.rvt | RVT (152.05Mo)