

Naziv PDF datoteke



X-LIGHT 360 LEGRAND

X-Light 360 Recessed emergency lighting permanent - non perm 100 lumens 1h standard

REF. 660042 | EAN KODA. 3414972238793

> [The product details page](#)

Značilnosti izdelka:

- Standard Version
- Lumen output : 100
- Duration : 1H
- Operating mode: Maintained (M)/Non-maintained (NM)

Prednosti montaže:

- Removable terminal (plug-in) allowing quick installation

Edinstvene značilnosti:

- Thanks to QR code engraved on emergency lighting unit, you have an instant access to data sheet, technical information... etc
- X-light 360 offers a discreet solution for perfect integration into all types of buildings with Thickness 2 mm
- Our packaging are 100% recyclable 0 Plastic and made at 80% from recycled carton

Dokumentacija

Tehnična dokumentacija

- LE13296AD.pdf | PDF (0.56Mo)
- S000118532FR_3.pdf | PDF (3.96Mo)
- S000118532EN_3.pdf | PDF (3.96Mo)

CAD & specifikacije načrtov / BIM

- URA SPOT Standard - Permanent_Non Permanent.rfa | RFA (1.16Mo)
- URA SPOT Standard - Permanent_Non Permanent-ENG.rfa | RFA (1.16Mo)

Katalog & drugo

- ex223001_0905.pdf | PDF (0.06Mo)
- LG-660042.zip | ZIP (0.02Mo)

Pogodbe in certifikati

- AENOR S-007/000004 | (0.91Mo)
- AENOR-007/001913 | (0.9Mo)
- OC / CB-ES2591-M1-AENOR | (0.41Mo)
- ENEC-ENEC/001218 | (0.46Mo)
- ENEC-ENEC/001218 | (0.5Mo)
- LGRP-01887-V01.01-EN.pdf | PDF (0.85Mo)