

Naziv PDF datoteke



X-LIGHT 180 LEGRAND

X-Light 180 emergency light surface permanent - non perm 70lm 1h std

REF. 660071 | EAN KODA. 3414972239035

> [The product details page](#)

Značilnosti izdelka:

- Standard Version
- Lumen output : 70
- Duration : 1H
- Operating mode: Maintained (M)/Non-maintained (NM)

Prednosti montaže:

- Removable terminal (plug-in) allowing quick installation

Prednosti uporabe:

- 3 Installation Modes: Ceiling surface-mounted, Wall surface-mounted & Recessed ceiling (via an accessory 660195)

Edinstvene značilnosti:

- Thanks to QR code engraved on front face of emergency lighting unit, you have an instant access to data sheet, technical information... Etc
- X-light 180 offers a perfect integration into any architectural space. & propose a variety of accessories for weatherproof, signage, surface or recessed installation.
- Our packaging are 100% recyclable 0 Plastic and made at 80% from recycled carton

Dokumentacija

Tehnična dokumentacija



LE13939AA.pdf | PDF (0.35Mo)

CAD & specifikacije načrtov / BIM

URA NEXT Standard Export - Permanent_Non Permanent-Pose plafond.rfa | RFA (1.33Mo)

URA NEXT Standard Export - Permanent_Non Permanent-Ceiling Mounted.rfa | RFA (1.33Mo)

URA NEXT Standard Export - Permanent_Non Permanent-Wall Mounted.rfa | RFA (1.13Mo)

Katalog & drugo



ex223001_0910.pdf | PDF (0.08Mo)



LG-660071.zip | ZIP (0.02Mo)

Pogodbe in certifikati



AENOR-007/001914 | (1.1Mo)



OC / CB-ES2592-M1-AENOR | (0.59Mo)



ENEC-ENEC/001219 | (0.59Mo)

URA NEXT Standard Export - Permanent_Non Permanent-Pose
murale.rfa | RFA (1.13Mo)