

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Universal dimmer with neutral 3 wires 150W white

REF. 078408A | EAN KODA. 3414972446501

This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

> [The product details page](#)

Splošni opis:

This universal light dimmer supports all "Dimmable" type bulbs on the market, LEDs, Halogens, Fluocompact, etc. It allows you to create a luminous atmosphere while reducing your energy consumption.

Značilnosti izdelka:

- Allows you to control Dimmable bulbs of the market, LEDs, halogen, compact fluorescent
- Power : 150W max. Dimmable Leds/Fluocompact/Halogen
- Compatible box depth 40mm
- White

Prednosti montaže:

- Auxiliary entry for mechanical push-button control

Prednosti uporabe:

- Universal dimmer - Upper and lower light adjustment

Edinstvene značilnosti:

- Universal dimmer. Compatibility with a wide range of "Dimmable" LED bulbs

Dokumentacija

Tehnična dokumentacija

 F03676EN-02.pdf | PDF (1.17Mo)

 LE13991AB.pdf | PDF (2.16Mo)

 F03676FR-02.pdf | PDF (1.18Mo)

Pogodbe in certifikati

 OC / CB-HU-005072 | (0.6Mo)

Katalog & drugo

 ex223001_1177.pdf | PDF (0.07Mo)