

Naziv PDF datoteke



SYNERGY™ LEGRAND

Synergy™ - 1 gang single pole unswitched outlet - with USB A 15W charger - White

REF. 730078A | EAN KODA. 3414972429207

> [The product details page](#)

Značilnosti izdelka:

- 2P+E British Standard, 13A, 250V + 3A 15W USB charger Type A
- Conform to BS1363 - 2USB charger conform to IEC62368 and IEC62680
- Screw type terminals for a secured & enhanced contacts
- Cover plate is square 86x146 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Priporočila / omejitve

- Recommended inside use only

Prednosti montaže:

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Prednosti uporabe:

- Two in One product : Power outlet, fitted with safety shutters to maximise child protection + Convenient charging of USB devices

Edinstvene značilnosti:

- Plate and switch rocker in same metal: Stainless steel rust resistance
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Dokumentacija

Tehnična dokumentacija

F03970EN-00.pdf | PDF (0.78Mo)

Pogodbe in certifikati

G-MARK-0048-1054-V-2 | (13.93Mo)

OC / CB-SE-108599 | (1.79Mo)

Katalog & drugo

ex223001_0718.pdf | PDF (0.09Mo)