

Naziv PDF datoteke



VALENA LIFE LEGRAND

Time delay switch without neutral Valena In'Matic - 10 AX 250 V~

REF. 752061 | EAN KODA. 3414970463562

> [The product details page](#)

Značilnosti izdelka:

- Valena™ IN'MATIC mechanisms - switches - Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting - Supplied with mounted dust protection transparent shield - To be equipped with Valena Life or Valena Allure cover plates and plates - Packaged in boxes
- Switches 10 AX - 250 V~Time delay switch, without neutral - Screw terminals - Accepted power by lamp type: - - ELV halogen with ferromagnetic or electronic transformer: 400 VA - 230 V halogen and incandescent: 1000 W - Fluorescent tubes with ballast: 400 VA - Motor (e.g: ventilation): 250 VA - Time delay setting from 25 s to 15 min - The switch incorporates a LED for the illumination function (locator)

Dokumentacija

Tehnična dokumentacija



LE07428AA.pdf | PDF (1.49Mo)

CAD & specifikacije načrtov / BIM



752061_AIICATPart.stp | IFC (13.76Mo)