

Naziv PDF datoteke



LEGRAND

Manual call point for fire detection/alarm system - conventional -1 NO/NC -5 A -24 V= -RAL 3000

REF. 138069 | EAN KODA. 3414970520531

> [The product details page](#)

Značilnosti izdelka:

- Safety boxes 90 series - for fire detection and fire alarm system, emergency exit, extinguishing system, remote switching
- Manual call points (MCP) - IP 30 - IK 07 - Surface - mounting or flush-mounting (IP 30) - Dimensions : 90x90x57 mm (surface - mounting with its base) or 90x90x24 mm (flush-mounting with flush boxes for wiring devices - drilling diameter 67 mm - for 60 mm Fixing centres) - Can be fitted on trunking Cat. Nos 0 104 63/64, 35x105 mm or 50x105 mm, with the universal support Cat. No 0 109 13 - Call by pressing the membrane (pressure 2.5 kg) with clear display of the call position - Reset on Front of device, with special key Cat. No 0 380 38 (supplied with the product) - Possibility to add an optional mechanical status indicator Cat. No 1 380 93 to provide additional signalling - Can receive a sealable cover Cat.No 0 380 97 MCP for fire detection and fire alarm systems - Conform to EN 54 - 11 standard - CE - CPR approved - Type A simple action - Color of the mechanical enclosure : red RAL 3000 - MCP - conventional - 1 contact - Equipped with 1 NO/NC contact 5 A 24 VDC

Dokumentacija

Tehnična dokumentacija



LE07336AB.pdf | PDF (2.11Mo)

Pogodbe in certifikati



LGRP-00302-V01.01-EN.pdf | PDF (0.61Mo)

Katalog & drugo



ex223001_0919.pdf | PDF (0.07Mo)