

Naziv PDF datoteke



VALENA LIFE LEGRAND

Floor heating thermostat Valena In'Matic - screw/claw mounting

REF. 752034 | EAN KODA. 3414970540928

> [The product details page](#)

Značilnosti izdelka:

- Valena™ IN'MATIC mechanisms - thermostats and ventilation controls - Valena In'Matic mechanisms are supplied with metal support, for claw or screw mounting - To be equipped with Valena Life or Valena Allure cover plates and plates - Supplied with mounted dust protection transparent shield - Packaged in boxes
- Thermostats - Screw terminalsFloor heating thermostat - With one potential-free N/O contact and LED - 16 A ~ 230 V~ - Adjustable range from 10 °C to 60 °C - Supplied with 4 m floor sensor (max. sensor length 20 m) - Automatic freeze protection below 7 °C

Dokumentacija

Tehnična dokumentacija

 LE07427AE.pdf | PDF (1.04Mo)

CAD & specifikacije načrtov / BIM

 752033_AllCATPart.stp | IFC (13.7Mo)