

Naziv PDF datoteke



PRACTIBOX S LEGRAND

Practibox S flush-mounting DIN cabinet for masonry wall - 1 row of 8 modules - Smoked door - Earth terminal blocks

REF. 134058 | EAN KODA. 3414971218390

[> The product details page](#)

Značilnosti izdelka:

- Delivered with cover, door, chassis and DIN rail. Earth terminal blocks included.
- Practibox S is a guarantee of a high - quality range which complies with the IEC 60670 - 24 standard and allows installations compliant with IEC 61439 - 3 standard.
- Practibox S plastic cabinet has an IP40 and an IK70, protecting it from impacts and solid bodies larger than 1 mm. Flush-mounting box for masonry wall resist to incandescent wire up to 650°C.
- Reversible cabinet and door allowing openings to the left or to the right according to the room configuration. The Practibox S door opens to 180°.
- Option of joining cabinets with a dedicated kit (ref. 134102) and a key lock (ref. 134100). Different kind of terminal blocks are available as accessories in order to upgrade your cabinets according to your needs (ref. 1348xx)

Priporočila / omejitve

- Indoor installation only. Integration of DIN modular devices up to 63A

Prednosti montaže:

- Practibox S by Legrand have an optimised wiring space thanks to comfortable cabling spaces on all sides, a 150mm between DIN rails and a removable frame allowing wiring in the workshop. A dedicated joining kit, also available as an accessory, allows an easy assembly for flush-mounting cabinets. Also, a cut-out on the back of the packaging can be used to protect the flush-mounting box during installation.

Prednosti uporabe:

- Practibox S cabinets have an attractive and modern appearance designed for the residential sector, both houses and flats, and for small office buildings. The cabinets can be delivered with a white door which blends harmoniously into any interiors and gives an aesthetic touch in your home or commercial shop. The smoked door is also available in order to easily verify if your installation is operating correctly.

Edinstvene značilnosti:

- Thanks to an extensive offer scope from 4M to 72M, Practibox S cabinets cover a large range of needs on your work sites. They are adapted to any configuration regardless of the type of installation, flush-mounted or surface-mounted, in residential or small office buildings.

Dokumentacija

Tehnična dokumentacija



F02633FR-03.pdf | PDF (1.18Mo)

Katalog & drugo




ex223001_0315.pdf | PDF (0.06Mo)

 LE10835AA.pdf | PDF (3.9Mo)

 F02633EN-03.pdf | PDF (1.22Mo)


CAD & specifikacije načrtov / BIM

 134058.dwg | DWG (1.94Mo)

 ex223001_0312.pdf | PDF (0.07Mo)

Pogodbe in certifikati

 LOVAG-IT 22.008 | (1.04Mo)

 LGRP-00899-V01.01-EN.pdf | PDF (0.64Mo)

 OC / CB-FR_703887/A1 | (1.45Mo)