

Naziv PDF datoteke



LEGRAND

Stainless steel Lid + Trim of standard floor box for wiring devices supports 8M vertical or 12M horizontal

REF. 088003 | EAN KODA. 3414970754967

> [The product details page](#)

Značilnosti izdelka:

- Accepts all kind of coating with maximum 8mm thickness.
- Removable Lid to facilitate connections to the wiring devices
- Rigid cable exit in metal, with a retaining stop in opening position and a foam to protect cords.
- Discreet and easy opening by one hand thanks to its central button.
- Once mounted, the floor box have a global load resistance 5000N (vertical load applied through a large surface diam, 130mm)

Priporočila / omejitve

- Indoor use only.

Prednosti montaže:

- Floor box modular to compose : matchs with your needs (type of installation, number of modules, finishes), gives time for reflexion, protects the product during the progression of the work site (the installation follows the steps of the site).

Prednosti uporabe:

- Two possible orientations for the cable exit : Lid and Trim easily reversible to 180 degrees

Edinstvene značilnosti:

- A universal range available in three sizes, adapted to any kind of floor (raised floors, screed floors) and upgradable because equipped with commons wiring devices supports (a standard floor box can become a flush one without touching the electrical connexions).
- Installation without tool : clips-on and unclips easily in the support kit : quick mounting and inexpensive maintenance.
- Association of metal lid robustness and brushed Stainless steel elegance.

Dokumentacija

Tehnična dokumentacija

-  LE09677AA-03.pdf | PDF (2.3Mo)
-  F03331FR-03.pdf | PDF (4.42Mo)
-  F03331EN-03.pdf | PDF (4.4Mo)
-  F03334EN-03.pdf | PDF (6.96Mo)

Katalog & drugo

-  ex223001_1143.pdf | PDF (0.46Mo)
-  ex223001_1140.pdf | PDF (0.12Mo)
-  ex223001_1144.pdf | PDF (0.05Mo)
-  ex223001_1142.pdf | PDF (0.51Mo)

 F03334FR-03.pdf | PDF (7.11Mo)

CAD & specifikacije načrtov / BIM

- Legrand_universal_round_floor_boxes_EN.rfa | RFA (1.09Mo)
- Legrand_boites_de_sol_univ_affleurant_FR.rfa | RFA (1.45Mo)
- legrand_boites_de_sol_univ_vers_rde_FR.rfa | RFA (1.09Mo)
- Legrand_universal_std_floor_boxes_NL.rfa | RFA (1.49Mo)
- Legrand_universal_std_floor_boxes_EN.rfa | RFA (1.46Mo)
- Legrand_universal_flush_floor_boxes_NL.rfa | RFA (1.45Mo)

 3D_LG-088003.stp | IFC (9.28Mo)

- Legrand_universal_flush_floor_boxes_EN.rfa | RFA (1.45Mo)
- Legrand_universal_round_floor_boxes_NL.rfa | RFA (1.09Mo)
- legrand_boites_de_sol_univ_vers_std_FR.rfa | RFA (1.46Mo)

Pogodbe in certifikati

 LGRP-00109-V01.01-EN.pdf | PDF (0.61Mo)