

Naziv PDF datoteke



LEGRAND

Emergency luminaire B65 - autotest/address
maint./non maint. - 100 lm - 3h - LED

REF. 662440 | EAN KODA. 3414970312570

> [The product details page](#)

Značilnosti izdelka:

- B65 LED - weatherproof self - contained emergency lighting luminaire LED - Weatherproof LED maintained and non-maintained units - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs. IP 65 - IK 07 - Plug - in base to ease fixing, cabling and connection - Duration : 1 and 3 hours. Ni - Cd or Ni - MH batteries. Recharge time : 24 hours - Charge monitor with a green LED. Power supply : 230 V $\pm$ 10% - 50/60 Hz. Class II - High - capacity screw terminals (2 x 2.5mm²) - 3 flexible cable entries for 16, 20 and 25 mm tubes - Can be equipped with metallic protection grids Cat.Nos 0 626 90/92
- Autotest and addressable luminaires - Maintained/non-maintained (M/NM) - Autotest/addressable luminaires incorporate an automatic self - testing system in order to check emergency lighting - Tests result is visible on 2 signalling LEDs (green - OK and yellow - defective) - Addressable function is activated by setting an ID on each luminaire with configuration tool (Cat.No 0 626 10) and wiring a complementary BUS line - Operating state of all addressable luminaires can be centralized by the control interface (Cat.No 0 626 00) and monitored on a local touch screen controller (Cat.No 0 626 01), or with the building€™s plan on Legrand Vision System (LVS2) PC software Cat.No 0 626 02 - These Maintained luminaires can also operate in non-maintained mode according to the wiring of normal lighting - 100 lm - 3h (LEDs)

Dokumentacija

Tehnična dokumentacija

-  S000083090EN-3.pdf | PDF (3.47Mo)
-  LE06964AE.pdf | PDF (0.53Mo)
-  S000083090FR-3.pdf | PDF (3.67Mo)

CAD & specifikacije načrtov / BIM

Legrand_Emergencia_B65LED_EN.rfa | RFA (0.51Mo)

Katalog & drugo

-  ex223001_0911.pdf | PDF (0.05Mo)
-  Legrand 662440 B65LED 100LM-3H M.zip | ZIP

Pogodbe in certifikati

-  AENOR S-007/000004 | (0.91Mo)
-  ENEC-ENEC/000993 | (0.48Mo)