

Naziv PDF datoteke



LCS³ LEGRAND

Patch panel 19 inch - to be equipped with cassettes and 24 RJ45

REF. 033791 | EAN KODA. 3414970870803

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

> [The product details page](#)

Splošni opis:

This 19 inch patch panel has a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

Značilnosti izdelka:

- Equipped with rear cable guide to hold the cables.
- 19" panel - 1 U.
- Supplied with coloured labels, white yellow, blue and red.

Priporočila / omejitve

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

Prednosti montaže:

- Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for installation and maintenance. Universal and secured mounting on any cabinet or enclosure through new generation quick-fix anchorage. Automatic cassette removal by a simple button press. Hands-free cassette support during installation or maintenance while in the extracted position.

Prednosti uporabe:

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

Edinstvene značilnosti:

- Save time at both installation and in daily maintenance by taking advantage of the screwless mounting and the automatic removal of each cassette.

Dokumentacija

Tehnična dokumentacija

- LE09727AD.pdf | PDF (4.73Mo)
- S000104244EN-04.pdf | PDF (0.12Mo)
- S000099438FR-04.pdf | PDF (1.91Mo)
- S000099438EN-04.pdf | PDF (1.91Mo)

Pogodbe in certifikati

Katalog & drugo

- ex223001_0976.pdf | PDF (0.15Mo)
- ex223001_0978.pdf | PDF (0.16Mo)
- ex223001_0994.pdf | PDF (0.12Mo)
- ex223001_0989.pdf | PDF (0.16Mo)
- ex223001_0983.pdf | PDF (0.16Mo)

-  LGRP-00626-V02.01-FR.pdf | PDF (0.96Mo)
-  LGRP-00626-V02.01-EN.pdf | PDF (0.95Mo)