


Naziv PDF datoteke



LIVING NOW BTICINO

Living Now - 6 modules cover plate, NIGHT

REF. BT-KA4806DG | EAN KODA. 8005543614631

> [The product details page](#)

Značilnosti izdelka:

- Extreme purity of the design and precision of geometries
Living Now has a unique shape, compact, distinctive.
- Innovative design : perfect flatness of the switch thanks to a self - centering system of the covers that allows the controllers to always remain aligned to the plate, even after multiple drives.
- Floating Frame : a flexible frame, placed on the back of the cover plate, free to move on the four corners, ensuring an optimal installation. Thanks to the floating frame, Living Now seems fluctuating on the wall.
- 6 modules, bimaterial technopolymer, NIGHT finish
- Delivered with dedicated packaging to maintain the aesthetic characteristics unaltered

Priporočila / omejitve

- For internal use only.

Prednosti montaže:

- The Living Now cover plate is equipped with a flexible frame, placed on the back of the plate, free to move on the four corners, ensuring an optimal installation.

Prednosti uporabe:

- Innovative Design: unique and compact shape that, completed with the covers, gives the switch an absolute flatness. The presence of shiny parts given by bimaterial technology, gives lightness to the object and depth in the finishes.

Edinstvene značilnosti:

- Innovative Design: unique and compact shape that, completed with the covers, gives the switch an absolute flatness
- Floating frame: a flexible frame, placed on the back of the plate, free to move on the four corners, which guarantees an optimal installation by masking the imperfections of the wall or in the case of plasterboard boxes.
- The separation between the aesthetic and functional parts allows to finish the installation in a workmanlike manner avoiding scratches or dirtying

Dokumentacija

Tehnična dokumentacija



F02845EN-01.pdf | PDF (0.59Mo)

Pogodbe in certifikati

CAD & specifikacije načrtov / BIM

BIM-BTICINO-LIVING-NOW-2025-ENGLISH.rvt | RVT (152.05Mo)



AENOR-030/002589 | (0.29Mo)